

ROOTT N-line Multiunits												
4.8 mm Platform M 1.4 Screw		Osstem* Mini/Narrow	Osstem* Regular	Biohorizon*Wide	Biohorizon* Regular	Neodent Standard Grand Morse	Nobel Biocare Regular	Nobel Biocare Narrow	Straumann BLX	Straumann BL/BLT	Megagen Anyridge	Megagen Blue Diamond
Straight												
	N1	KM-N1	K-N1	IW-N1	I-N1	NE-N1	NO-N1	NP-N1	SX-N1	SB-N1	MG-N1	MB-N1
	N2	KM-N2	K-N2	IW-N2	I-N2	NE-N1	NO-N2	NP-N2	SX-N2	SB-N2	MG-N2	MB-N2
	N3	KM-N3	K-N3	IW-N3	I-N3	NE-N1	NO-N3	NP-N3	SX-N3	SB-N3	MG-N3	MB-N3
	N4	KM-N4	K-N4	IW-N4	I-N4	NE-N1	NO-N4	NP-N4	SX-N4	SB-N4	MG-N4	MB-N4
15°												
	N1A15	KM-N1A15	K-N1A15	IW-N1A15	I-N1A15	NE-N1A15	NO-N1A15	NP-N1A15	SX-N1A15	SB-N1A15	MG-N1A15	MB-N1A15
	N2A15	KM-N2A15	K-N2A15	IW-N2A15	I-N2A15	NE-N1A15	NO-N2A15	NP-N2A15	SX-N1A15	SB-N1A15	MG-N1A15	MB-N1A15
	N3A15	KM-N3A15	K-N3A15	IW-N3A15	I-N3A15	NE-N1A15	NO-N3A15	NP-N3A15	SX-N1A15	SB-N1A15	MG-N1A15	MB-N1A15
	N4A15	KM-N4A15	K-N4A15	IW-N4A15	I-N4A15	NE-N1A15	NO-N4A15	NP-N4A15	SX-N1A15	SB-N1A15	MG-N1A15	MB-N1A15
30°												
	N1A30	KM-N1A30	K-N1A30	IW-N1A30	I-N1A30	NE-N1A30	NO-N1A30	NP-N1A30	SX-N1A30	SB-N1A30	MG-N1A30	MB-N1A30
	N2A30	KM-N2A30	K-N2A30	IW-N2A30	I-N2A30	NE-N2A30	NO-N2A30	NP-N2A30	SX-N2A30	SB-N2A30	MG-N2A30	MB-N2A30
	N3A30	KM-N3A30	K-N3A30	IW-N3A30	I-N3A30	NE-N3A30	NO-N3A30	NP-N3A30	SX-N3A30	SB-N3A30	MG-N3A30	MB-N3A30
	N4A30	KM-N4A30	K-N4A30	IW-N4A30	I-N4A30	NE-N4A30	NO-N4A30	NP-N4A30	SX-N4A30	SB-N4A30	MG-N4A30	MB-N4A30
45°												
	N1A45	KM-N1A45	K-N1A45	IW-N1A45	I-N1A45	NE-N1A45	NO-N1A45	NP-N1A45	SX-N1A45	SB-N1A45	MG-N1A45	MB-N1A45
	N2A45	KM-N2A45	K-N2A45	IW-N2A45	I-N2A45	NE-N2A45	NO-N2A45	NP-N2A45	SX-N2A45	SB-N2A45	MG-N2A45	MB-N2A45
	N3A45	KM-N3A45	K-N3A45	IW-N3A45	I-N3A45	NE-N3A45	NO-N3A45	NP-N3A45	SX-N3A45	SB-N3A45	MG-N3A45	MB-N3A45
	N4A45	KM-N4A45	K-N4A45	IW-N4A45	I-N4A45	NE-N4A45	NO-N4A45	NP-N4A45	SX-N4A45	SB-N4A45	MG-N4A45	MB-N4A45
60°												
	N1A60	KM-N1A60	K-N1A60	IW-N1A60	I-N1A60	NE-N1A60	NO-N1A60	NP-N1A60	SX-N1A60	SB-N1A60	MG-N1A60	MB-N1A60
	N2A60	KM-N2A60	K-N2A60	IW-N2A60	I-N2A60	NE-N2A60	NO-N2A60	NP-N2A60	SX-N2A60	SB-N2A60	MG-N2A60	MB-N2A60
	N3A60	KM-N3A60	K-N3A60	IW-N3A60	I-N3A60	NE-N3A60	NO-N3A60	NP-N3A60	SX-N3A60	SB-N3A60	MG-N3A60	MB-N3A60
	N4A60	KM-N4A60	K-N4A60	IW-N4A60	I-N4A60	NE-N4A60	NO-N4A60	NP-N4A60	SX-N4A60	SB-N4A60	MG-N4A60	MB-N4A60

* is a registered trademark of an independent third party

MUA Superstructures 4 mm (M-Platform)

ROOTT M-P > Healing Abutments



GFM0 Multi-unit healing abutment, ROOTT M/P, H0mm

GFM2 Multi-unit healing abutment, ROOTT M/P, H2mm

GFM4 Multi-unit healing abutment, ROOTT M/P, H4mm



GFNM0 Multi-unit healing abutment, narrow, ROOTT M/P, H0mm

GFNM2 Multi-unit healing abutment, narrow, ROOTT M/P, H2mm

GFNM4 Multi-unit healing abutment, narrow, ROOTT M/P, H4mm

ROOTT M-P > Transfers



TOM Transfer, ROOTT M/P, open tray, H11.5mm

TOML Transfer, ROOTT M/P, open tray, long, H20.5mm

TRM-MP Transfer, ROOTT M/P, closed tray, with TC cap, H11mm



ROOTT M-P > Transfers > Dragon Scan

SPCOMIO Dragon Scan post, ROOTT M/P



ROOTT M-P > Analogs

ANM Implant analog, ROOTT M/P, reverse scan, H9.5mm

ROOTT M-P > Titanium Bases



PCOM Titanium base, ROOTT M/P, H5.5mm

PCOMR Titanium base, ROOTT M/P, rotational, H5.5mm

SFPCOM Prosthetic screw, ROOTT M/P titanium base



ROOTT M-P > Titanium Bases > Temporary

AM Temporary multi-unit Ti-base, ROOTT M/P, H11mm



ROOTT M-P > Burn-out Abutments

ABMU Burn-out abutment, ROOTT M/P, straight, H9mm

ABMUA Burn-out abutment, ROOTT M/P, 15° angled, H9mm

MUA Superstructures 4.8 mm (N-Platform)

ROOTT R > Abutments N > Gingiva Formers



NGFM0 Multi-unit healing abutment, N-MUA platform, H4mm

NGFM2 Multi-unit healing abutment, N-MUA platform, H5mm

NGFM4 Multi-unit healing abutment, N-MUA platform, H6mm



NGFNM0 Multi-unit healing abutment, N-MUA platform, narrow (locator), H4mm

NGFNM2 Multi-unit healing abutment, N-MUA platform, narrow (locator), H5mm

NGFNM4 Multi-unit healing abutment, N-MUA platform, narrow (locator), H6mm

ROOTT R > Abutments N > Transfers



NTOM Transfer, N-MUA platform, open tray

NTOML Transfer, N-MUA platform, open tray, long

NTRM Transfer, N-MUA platform, closed tray, with TC cap



ROOTT N > Transfers > Dragon Scan

NSPCOMIO Dragon Scan post, N-MUA platform



ROOTT R > Abutments N > Analogs

NANM Implant analog, N-MUA platform

ROOTT R > Abutments N > Titanium Bases



NPCOMR Titanium base, N-MUA platform, H5.8mm

SNFPCOM Prosthetic screw, N-MUA platform, titanium base, 3.7mm



NAM Temporary multi-unit Ti-base, N-MUA platform



ROOTT R > Abutments N > Burn-out Abutments

NABMU Burn-out abutment, N-MUA platform, straight

Biohorizon Standard Internal Hex (2.42 - 2.43 mm)

Compatible Brands

Zimmer Biomet	Zimmer Biomet: Screw-Vent / TSV internal-hex family.
MIS Implants	MIS Implants: SEVEN / internal-hex systems.
Alpha-Bio Tec	Alpha-Bio Tec: Internal Hex line.
Adin	Adin: Compatible with multi-brand internal-hex listings.
AB Dental	AB Dental: Devices are listed as compatible with the internal-hex standard platform.
Cortex	Cortex: Appears in internal-hex compatibility groups.
Implant Direct	Implant Direct: Legacy / InterActive internal-hex lines.
ERM Dental	ERM Dental: Titan+ internal-hex implants.
DSI (Dental Solutions Israel)	DSI (Dental Solutions Israel): Standard prosthetic kit confirms regular internal hex of 2.42 mm.
GDT Implants	GDT Implants: Standard platform internal hex is marketed for 2.42 mm connections.
DMi Innovative Medical Technology	DMi InNO-vative Medical TechNO-logy: Unique, Prima and Ideal titanium implants specify an internal hex of 2.43 mm.
Surcam Dental	Surcam Dental: A-Type, C-Type, SC-Type and S-Type implants are described as "internal hex 2.43".
Advan / ATiM	Advan / ATiM: Prosthetic protocol states "Internal Hex 2.43 mm".
BHI Implants	BHI Implants: Cyclone and compatible AB Dental platform implants feature a Zimmer-style hex.
MSDI	MSDI: Sells implant analogs compatible with 2.42 mm internal hexes.
Noris Medical	NO-ris Medical: Internal Hex Implant Lines, Tuff™ Series, Onyx™, Cortical™, PteryCore™, PteryFit™, and Zygomatic™ feature an internal hex connection of 2.42 mm.
Paltop	Paltop: Standard Platform (SP) implant lines, including Advanced, Advanced+, Dynamic, PAI Total Coverage (TC), and PAI, use a 2.42 mm internal hex connection.
BioHorizons	BioHorizons: The Tapered Internal line and standard platforms are widely referenced in compatibility charts for 2.42/2.43 internal hex.
Alfa Gate	Alfa Gate: Standard platform internal hex line.
Alpha Dent	Alpha Dent: Internal hex standard platform.
Blue Sky Bio	Blue Sky Bio: Internal hex platform options.
Ditron	Ditron: Included in standard internal hex cross-compatibility.
Edison Medical	Edison Medical: Included in internal hex platform compatibility.
iRes	iRes: Mentioned alongside other major internal hex brands.
JDentalCare	JDentalCare: Internal hex compatible standard platforms.
Ritter Implants	Ritter Implants: Internal hex platforms.
SGS Dental Implants	SGS Dental Implants: Standard internal hex connections.

Osstem Compatible Brands

Osstem (Compatible Brands)
Hiossen
DIO
Dentium
NeoBiotech
Megagen Anyone
Evidence Implant (Korea)
I-DO / Oneday Biotech
iRES